

## VETRONIC MERLIN SMALL ANIMAL VENTILATOR

VSL-MERLIN



Category: Winter Sale > Ventilators > Anaesthesia Accessories > Anaesthesia > Veterinary

Sale Price: £4,500.00

Price: £5,457.38

Date Printed: 17/04/24

### PRODUCT DESCRIPTION

## One ventilator for all your small animal practice needs, from small rodents to large dogs.

The Vetronic Merlin veterinary ventilator has been designed with just that in mind. Using the latest technology, Merlin is able to precisely control ventilation parameters to ensure your patient is as safe as can be during mechanical ventilation. Merlin doesn't require a compressed gas supply to operate, so is quiet and smooth. And, because Merlin is controlled by a state-of-the-art microcontroller, you can confidently set the independent ventilation parameters that you want, without compromise.

Merlin is a microprocessor-controlled ventilator, designed by vets for vets. We have done away with the conventional pressurised gas driving mechanism. This new ventilator uses a precisely-controlled piston that can accurately delivery volumes in the range 1ml to 800ml.

Merlin can be pressure cycled, volume cycled or time cycled and the inspiratory and expiratory times are fully and independently variable, without the need to re-adjust after changes in flow rates or volumes. A pressure control allows you to set the maximum allowable pressure during volume cycling, or the target pressure during pressure cycling.

A further added feature is the inspiratory assist control that will tune the ventilator to your patient during recovery and so assist weaning from the ventilator. On the front of the unit is a large, easily-readable display that shows all of your selected parameters. The parameters are continuously updated, reflecting every adjustment made.

In addition, we believe Merlin is truly innovative in being the first veterinary ventilator to calculate and display the compliance of the patient being ventilated.

**The Merlin comes supplied with everything you need to use the unit out of the box, including:**

1 x IEC Power Lead: UK/ EU/ US/ AU

1 x Operating Manual

1 x Tidal Volume Chart / Flow Rate Chart  
 1 x "Exhaust gas setup for Merlin Ventilator" document  
 1 x MERL-0001 Merlin Common Scavenge set (Gas Out)  
 1 x MERL-0002 Merlin Gas Inlet set  
 1 x MERL-0003 Merlin Low-dead space set  
 1 x MERL-0006 Merlin Circle Connection kit  
 1 x CIRSBC15 Smooth Bore Y-Circuit 15mm x 1.8m  
 1 x CIRSBC222 Smooth Bore Y-Circuit 22mm x 1.8m  
 1 x VS0230 22M-22F with one-way valve – to patient  
 1 x VS0232 22M-22F with one-way valve – from patient

### Key features:

- Precise, reliable control over all ventilation parameters
- Fits into rebreathing and non-rebreathing circuits
- Pressure cycled, time cycled or volume cycled IPPV
- Patient disconnect and over-pressure alarms
- 80-character screen and high-definition LEDs give full parameter information:
  - Tidal volume
  - Minute volume
  - Inspiratory and expiratory airway pressure
  - I:E ratio
  - Patient compliance
  - Respiratory rate
  - Inspiratory time
  - Expiratory time
  - Maximum allowed airway pressure
  - Assist effort
- Purpose-designed stainless steel and silicon valves for precise flow control
- Standard 22mm/15mm fittings
- Suitable for anaesthesia or ICU
- Mains powered with fail-safe operation
- Assist mode

### Mechanical

Overall dimensions:	45 x 20 x 34cm
Weight:	17kg
Construction:	Enamelled steel box with feet

### Electrical

Power supply:	230 Volts AC 50Hz mains only, European and US versions available
Supply current:	250mA
Power Consumption:	60 watts
Rear panel fuse rating:	1 amps antisurge
Plug fuse rating:	5 amps

### General

Mode of operation:	Microprocessor-controlled precision piston
--------------------	--

Capacity:	1mL to 40mL, in 1mL increments
	40mL to 120mL, in 5mL increments
	120mL to 800mL, in 10mL increments
Flow rates:	0.1 to 3.5L/minute, in 0.1L increments
	3.5 to 25.0L/minute, in 0.5L increments
Inspiratory/expiratory times:	0.5 to 9.0 seconds, in 0.1 second increments
Pressure settings:	1 to 57cm H2O pressure, in 1cm H2O increments
Inspiratory assist setting:	-1 to -10cm H2O pressure, in 1cm H2O increments
Valves:	Electrically-operated solenoid valves, stainless steel and silicon construction
LCD module:	Backlit 80-character, four-line display
Alarm mode:	Audible: 2kHz buzzer
Gas connections:	Front fixing 22mm O/D, 15mm I/D, stainless steel ports
Power failure mode:	All valves open. Manual IPPV can be performed

## ADDITIONAL INFORMATION

<b>Animal</b>	Small Animal
<b>SKU</b>	VSL-MERLIN

### Good to know...

At Burtons we know you have a choice to shop with us, that is why we always aim to delight our customers with a fast, easy, shopping experience. Making and sourcing only the best products we can find to fit your needs.

**Price Matching:** We regularly check all our prices against competitors so you don't have to. If you do find a like for like product cheaper we will aim to not just match it, but beat it!

**Backorders:** All back ordered items will be ordered and shipped as quickly as we can to you. Special order items may take up to 4 weeks. Once ordered a member of our team will be in contact to keep you informed of estimated delivery dates.

**Returns Policy:** You may return new, unworn or unused products within fourteen (14) days of delivery for a full refund of the cost of the goods, or an exchange if preferred. This is on top of your statutory rights