

## BURTONS EN-S7P SYRINGE DRIVER - CLEARANCE

EN-S7P-CL



## PRODUCT DESCRIPTION

### This multi-function syringe driver brings a whole new array of features and benefits

Do you love your Burton's EN-V5 infusion pump? We now have a syringe driver to match!

The EN-S7P Syringe Driver is perfectly adapted for veterinary use, working on both battery (with up to 12 hours of usage) and mains supply. This multi-function syringe driver brings a whole new array of features and benefits.

Incredibly easy & efficient to use, it automatically recognises a range of syringe sizes and stores up to 20 editable brands. The 4.3 colour touchscreen makes any editing and parameter settings incredibly easy to do.

#### Featuring multi-function operation with 3 modes: ml/h (time, rate mode); Body-weight mode and Micro-mode

- Automatic recognition of syringe sizes (5,10,20,30 and 50/60)
- Stores up to 20 editable brands
- 4.3-inch colour touch screen, parameter setting and editing directly on the screen
- Multi-function operation with 3 modes: ml/h (time, rate mode); Body-weight mode and Micro-mode
- Flow rates range from 0.01 ml/h to 1,500ml/h with increment of 0.01 ml/h
- KVO range from 0.01 to 5ml/h, editable
- Record more than 5000 logs
- 12 hours battery backup time
- IP24 waterproof, and stackable design

#### Specifications:

- Screen: 4.3 inches LCD colour touchscreen

- Syringe types: 2/3ml, 5ml, 10ml, 20ml, 30ml, 50/60ml – Open systems, automatic recognition of syringe brands and sizes after calibration
- Infusion mode: ml/h (include rate mode, Time mode) Body weight mode
- Flow rate range: 0.01-2000ml/h (min.increment 0.01ml/h)
- VTBI: 0-9999ml
- KVO: 0.01-5ml/h adjustable
- Bolus rate: 0.1-2000ml/h adjustable
- Occlusion Level: 4 levels selectable
- Interface: MINI USB
- Wireless: WiFi (optional)
- Alarm Type: VTBI Infused, Syringe empty, Pressure high, Battery empty, Check syringe, KVO finished, VTBI near end, Syringe near empty, Battery near empty, Reminder alarm, No power supply, System error etc.
- AC Power: 110V-240V, 50/60Hz
- External DC Power: 12V
- Battery: Lithium Polymer Battery 11.1V 2600mAh – More than 12 hours operating time @ 5ml/h – Less than 5 hours fully charged.
- Dimensions: 400mmL x 90mmW x 120mmH
- Weight: Approx 1.7kg

S/N: 71220843871

## ADDITIONAL INFORMATION

<b>Animal</b>	Mixed
<b>SKU</b>	EN-S7P-cl
<b>Brand</b>	Burtons
<b>Battery</b>	Yes
<b>Screen Type</b>	Touchscreen
<b>Volume Control</b>	Yes
<b>Flow Rate</b>	0.01ml/h ~ 1500ml/h with increment of 0.01 ml/h

### Good to know...

At Burtons we know you have a choice to shop with us, that is why we always aim to delight our customers with a fast, easy, shopping experience. Making and sourcing only the best products we can find to fit your needs. Price Matching: We regularly check all our prices against competitors so you don't have to. If you do find a like for like product cheaper we will aim to not just match it, but beat it! Backorders: All back ordered items will be ordered and shipped as quickly as we can to you. Special order items may take up to 4 weeks. Once ordered a member of our team will be in contact to keep you informed of estimated delivery dates. Returns Policy: You may return new, unworn or unused products within fourteen (14) days of delivery for a full refund of the cost of the goods, or an exchange if preferred. This is on top of your statutory rights