

**ASTRAMAX HD WALL MOUNTED OPERATING LIGHT**

AMAX30FW

**PRODUCT DESCRIPTION**

Data Common To All Models		
Lux	1m	140,000
Colour Rendition Index	Ra	95
Colour Rendition (Red)	R9	98
Colour Temperature	Kelvin	3,700 - 5,000
LED Life	Hours	≥40,000 Hours
Power Consumption	Watts	<50
Endoscope Settings		5%
Beam Size	D10	140-310mm
Weight (Ceiling, Wall, Mobile)	15Kg, 11Kg, 30Kg	

**ADDITIONAL INFORMATION**

<b>Animal</b>	N/A
<b>SKU</b>	AMAX30FW
<b>Head Type</b>	Single

## Good to know...

At Burton's we know you have a choice to shop with us, that is why we always aim to delight our customers with a fast, easy, shopping experience. Making and sourcing only the best products we can find to fit your needs.

**Price Matching:** We regularly check all our prices against competitors so you don't have to. If you do find a like for like product cheaper we will aim to not just match it, but beat it!

**Backorders:** All back ordered items will be ordered and shipped as quickly as we can to you. Special order items may take up to 4 weeks. Once ordered a member of our team will be in contact to keep you informed of estimated delivery dates.

**Returns Policy:** You may return new, unworn or unused products within fourteen (14) days of delivery for a full refund of the cost of the goods, or an exchange if preferred. This is on top of your statutory rights