

## M880B HANDHELD CAPNOGRAPH AND PULSE OXIMETER

129-880



### PRODUCT DESCRIPTION

## Ultra clear, ultra lightweight touchscreen Capnograph & Pulse Oximetry monitor. The perfect addition to any practice!

Boasting a large 4.3-inch, high resolution, auto-rotation touchscreen and a large capacity lithium battery. The M880B is designed for continuous monitoring or spot-checking of CO<sub>2</sub> and SPO<sub>2</sub> signals in patients.

#### Key Features:

- Extremely light, for carrying and handling €" Only 0.5KG with full configuration, including battery.
- 4.3" TFT high resolution with touch screen & auto-rotation for user ease of use with any orientation.
- Protection against ingress of liquid (IPX2 Waterproof)
- Specially designed water filter, ensuring humid environments don't effect readings
- Configurable for flux for horse, dog and cat
- Large capacity lithium battery for up to 18 hours use with 1.5m USB-C charging cable
- CO<sub>2</sub> start/off button to save power
- Selectable layout modes including font and waveforms
- Visual and audio alarm for exceeding limits and Apnea; pitch tone
- Optional CO<sub>2</sub> Sidestream - We recommend use of the optional CO<sub>2</sub> scavenging kit (V1175) - This will enable you to scavenge the small amount of anaesthetic agent present in the patient sample breath, utilising your current scavenging system

Size:	4.3inch
Resolution:	480*272
Touch:	Resistive Touch
Auto-rotation Direction	4 Direction
Power Adaptor:	Input: AC 100 V±2 240V Output: DC 5V/2A
CO <sub>2</sub> :	

Measurement Way:	Infrared Spectrum
Measurement Range:	0-19.7% (0-150mmHg 0-20kPA)
CO2 Accuracy:	<5.0% CO2 ±2mmHg >5.0% CO2 <6% of the reading
CO2 Resolution:	0.1mmHg
Gas Flow Rate:	60~80ml/min
Response Time:	1/2s
Calibration:	Offset calibration, auto/ manual; gain calibration
<b>SpO2</b>	
Measurement Range:	0~100%
Resolution:	1%
Accuracy:	70~100%± 2% 35~69%± 3% 0~34% definition

## ADDITIONAL INFORMATION

<b>Animal</b>	Small Animal
<b>SKU</b>	129-880
<b>Colour/Style</b>	White
<b>Brand</b>	BLT
<b>Monitor Parameters</b>	CO <sup>2</sup> , SpO <sup>2</sup>
<b>Screen Type</b>	Touchscreen
<b>Power Source</b>	Battery
<b>Optional Modules</b>	N/A

### Good to know...

At Burtons we know you have a choice to shop with us, that is why we always aim to delight our customers with a fast, easy, shopping experience. Making and sourcing only the best products we can find to fit your needs.

**Price Matching:** We regularly check all our prices against competitors so you don't have to. If you do find a like for like product cheaper we will aim to not just match it, but beat it!

**Backorders:** All back ordered items will be ordered and shipped as quickly as we can to you. Special order items may take up to 4 weeks. Once ordered a member of our team will be in contact to keep you informed of estimated delivery dates.

**Returns Policy:** You may return new, unworn or unused products within fourteen (14) days of delivery for a full refund of the cost of the goods, or an exchange if preferred. This is on top of your statutory rights